Keyence VHX-5000 Microscope

last updated: 7/17/25 Goose



Tool Type: Observation / measurement / imaging

Location: Elings 3430

Description: Microscope/camera **Manufacturer:** Keyence

About

The Keyence microscope is a semi computer controlled microscope that is capable of taking precision measurements from large depth of field images under high magnification. This microscope features both backlighting and top lighting, and has a computer controlled movable stage which can be used to pan across the object you are viewing. This microscope has a motorized objective which can be used to image parts with a large depth of field to create a single in focus image with depth mapping data. The motorized stage also allows for the stitching of several images to create larger high magnification pictures.

Safety Concerns

- Do not leave lighting elements on
- Do not crash the objectives
- If replacing the bulb in the MI-150 wear gloves to avoid getting oil on the halogen lamp bulb

Training Documentation

Keyence SOP

Detailed Specifications

- 17 mm/s Z travel
- Objective rotation up to 90 degree angle from normal stage axis
- Image stitching up to 20,000 x 20,000 pixels
- Optical zoom from o to 1000x
- 50 FPS max framerate

Reference Documentation

STL Converter Manual

Brochure

Field of View and Pixel Size Chart

Intermediate Quick Start Guide

Quick Start Guide

Exporting Keyence 3D data to STL

CSV to STL project documentation

(Matlab script to come)

VHX lenses

From:

https://microfluidics.cnsi.ucsb.edu/wiki/ - Innovation Workshop Wiki

Permanent link:

https://microfluidics.cnsi.ucsb.edu/wiki/doku.php?id=keyence_microscope

Last update: 2025/07/17 21:51

