


Keyence VHX-5000 Microscope

Keyence	
 A photograph of the Keyence VHX-5000 Microscope setup. It includes a black microscope unit on the left, a computer monitor in the center displaying a blue and white microscopic image, and a keyboard on the right. The entire setup is on a reflective white surface.	
Tool Type:	Observation and measurement
Location:	Microfluidics Lab
Description:	Microscope/camera
Manufacturer:	Keyence

About

The Keyence microscope is a semi computer controlled microscope that is capable of taking precision measurements from large depth of field images under high magnification. This microscope features both backlighting and top lighting, and has a computer controlled movable stage which can be used to pan across the object you are viewing. This microscope has a motorized objective which can be used to image parts with a large depth of field to create a single in focus image with depth mapping data. The motorized stage also allows for the stitching of several images to create larger high magnification pictures.

Safety Concerns

- Do not leave lighting elements on
- Do not crash the objectives
- If replacing the bulb in the MI-150 wear gloves to avoid getting oil on the halogen lamp bulb

Training Documentation

[Keyence SOP](#)

Detailed Specifications

- 17 mm/s Z travel
 - Objective rotation up to 90 degree angle from normal stage axis
 - Image stitching up to 20,000 x 20,000 pixels
 - Optical zoom from 0 to 1000x
 - 50 FPS max framerate
-

Reference Documentation

[STL Converter Manual](#)

[Brochure](#)

[Field of View and Pixel Size Chart](#)

[Intermediate Quick Start Guide](#)

[Quick Start Guide](#)

[Exporting Keyence 3D data to STL](#)

CSV to STL project documentation

(Matlab script to come)

[VHX lenses](#)

From:

<https://microfluidics.cnsi.ucsb.edu/wiki/> - **Innovation Workshop Wiki**

Permanent link:

https://microfluidics.cnsi.ucsb.edu/wiki/doku.php?id=keyence_microscope&rev=1672950304

Last update: **2023/01/05 20:25**

