

Table with alignment		
Item	Vendor	Notes
Fused silica capillaries with polyimide coating and luer fittings	<a href="#">World Precision Instruments</a>	Inlet / outlet fitting. Can be sealed to chips with hot glue or epoxy. Low dead volume.

From: <https://microfluidics.cnsi.ucsb.edu/wiki/> - Innovation Workshop Wiki

Permanent link: [https://microfluidics.cnsi.ucsb.edu/wiki/doku.php?id=microfluidics\\_suppliers&rev=1625006432](https://microfluidics.cnsi.ucsb.edu/wiki/doku.php?id=microfluidics_suppliers&rev=1625006432)

Last update: **2021/06/29 22:40**

