

# Trotec Speedy 100 30W Laser Cutter

## Trotec Speedy 100 Laser Cutter



**Tool Type:** Laser cutter

**Location:** Microfluidics Lab

**Description:** 30W laser cutter and engraver

**Manufacturer:** Trotec

## About

One of two laser cutters, the Trotec is located in the Innovations Workshop above its fume extractor. Both laser cutters utilize CorelDraw as a 2D sketch manager which is then imported into Trotec's specific cutting software. CorelDraw can be used to create the 2D sketch, however importing a DXF file or PDF into CorelDraw from Solidworks or other CAD packages is preferred due the CAD packages integrated features and functions.

## Safety Concerns

This laser engraving system contains a class 4 carbon dioxide (CO<sub>2</sub>) laser that emits intensive and invisible laser radiation. Without safety precautions the direct radiation or even diffuse reflected radiation is dangerous!

- Always wear safety glasses when using the machine.
- Always work with the machine cover closed.
- NEVER leave the laser machine alone when running a job. If you do need to leave,
- The machine door must be left open while you are away.
- Do not store any flammable materials in the inside of the device or in the immediate vicinity of the device.
- Remove leftovers of previously produced materials before running a job.
- A fire extinguisher/fire blanket must always be handy as the laser beam can ignite flammable materials.
- Metals, particularly un-coated aluminum, copper in particular, silver and gold, cannot be processed with the laser and lead to high reflections of the laser beam. If needed, metals can

be coated with a paint/tape which chemically bonds to the surface when engraved.

- Before processing materials the user must verify whether harmful materials can be generated and whether the filter equipment of the exhaust system is suitable for the harmful materials.
- PVC (polyvinyl chloride) must under no circumstances be processed with the laser.
- Looking directly into the laser can cause retinal damage.
- Confirm that the fume collection system is running whenever the laser is cutting or engraving.

---

## Training Documentation

[Laser Cutter Training SOP](#)

---

## Detailed Specifications

Work Area: 910 x 305 mm

Max Workpiece Height: 125 mm

Laser Power: 10-60 Watts

---

## Reference Documentation

[Marking Tape/Paint](#)

[Atmos Compact Operation Manual](#)

[Service Manual](#)

[Plastic Processing Guide](#)

[Job Control Software Manual](#)

[Bonding Acrylic with Methylene Chloride](#)

[Laser cutting data](#)

From:

<https://microfluidics.cnsi.ucsb.edu/wiki/> - Innovation Workshop Wiki

Permanent link:

[https://microfluidics.cnsi.ucsb.edu/wiki/doku.php?id=trotec\\_speedy&rev=1672889496](https://microfluidics.cnsi.ucsb.edu/wiki/doku.php?id=trotec_speedy&rev=1672889496)

Last update: **2023/01/05 03:31**

