Trotec Speedy 100 Laser Cutter

Trotec Speedy 100

Tool Type: Laser cutter
Location: Microfluidics Lab

Description: Laser cutter and engraver

Manufacturer: Trotec

About

One of two laser cutters, the Trotec is located in the Innovations Workshop above its fume extractor. Both laser cutters utilize CorelDraw as a 2D sketch manager which is then imported into Trotec's specific cutting software. CorelDraw can be used to create the 2D sketch, however importing a DXF file or PDF into CorelDraw from Solidworks or other CAD packages is preferred due the CAD packages integrated features and functions.

Safety Concerns

This laser engraving system contains a class 4 carbon dioxide (CO2) laser that emits intensive and invisible laser radiation. Without safety precautions the direct radiation or even diffuse reflected radiation is dangerous!

- Always wear safety glasses when using the machine.
- Always work with the machine cover closed.
- NEVER leave the laser machine alone when running a job. If you do need to leave,
- The machine door must be left open while you are away.
- Do not store any flammable materials in the inside of the device or in the immediate vicinity of the device.
- Remove leftovers of previously produced materials before running a job.
- A fire extinguisher/fire blanket must always be handy as the laser beam can ignite flammable materials.
- Metals, particularly un-coated aluminum, copper in particular, silver and gold, cannot be processed with the laser and lead to high reflections of the laser beam. If needed, metals can

be coated with a paint/tape which chemically bonds to the surface when engraved.

- Before processing materials the user must verify whether harmful materials can be generated and whether the filter equipment of the exhaust system is suitable for the harmful materials.
- PVC (polyvinyl chloride) must under no circumstances be processed with the laser.
- Looking directly into the laser can cause retinal damage.
- Confirm that the fume collection system is running whenever the laser is cutting or engraving.

Training Documentation

Laser Cutter Training SOP

Detailed Specifications

Unordered List ItemWorking area (W x D): 24 x 12 in

Max. height of workpiece: 5.2 in
Loading area (W x D): 27 in x 17 in

• Overall dimensions (W x D x H): 40 x 31 x 40 in

Max. processing speed: 110 ips
Max. acceleration: 1,969 ips²

• Technology motion system: Brushless DC servo motors

Laser power CO2: 30 - 60WLaser power fiber: 20 - 30 W

Laser class:2Weight: 150 kg

Power consumption: 1 ~ AC 110-230V 50/60Hz, 1.3 kW (60 watts)

Reference Documentation

Marking Tape/Paint

Atmos Compact Operation Manual

Service Manual

Plastic Processing Guide

Job Control Software Manual

Bonding Acrylic with Methylene Chloride

Laser cutting data

From:

https://microfluidics.cnsi.ucsb.edu/wiki/ - Innovation Workshop Wiki

Permanent link:

https://microfluidics.cnsi.ucsb.edu/wiki/doku.php?id=trotec_speedy&rev=1685566511

Last update: **2023/05/31 20:55**

